
DOG TROPHY

BIG 2021

USER GUIDE

EN





SUMMARY

CONTENT	4
DOGTROPHY 2021	5
HOW TO CHARGE	6
HOW TO START	7
ACCESSORIES (optional)	8
ATTENTION	9
RECYCLING	10
TECHNICAL SPECIFICATIONS	11
WARRANTY	12
CONFORMITY	13


CONTENT

- ▶ **DOGTROPHY** BIG 2021
- 3 BALLS (Diameter 90mm, Weight 79g)
- **► CHARGER**
- ► TRANSMITTER (PT3000) *
- ► FINGERKICK (BLUETOOTH RING) *
- **USER GUIDE**

* If included in the kit

DOGTROPHY 2021

- 1 PLASTIC TUBE
- **2** ON/OFF **BUTTON** AND **LED**
- **3** EXTERNAL **ANTENNA**
- **4** CHARGING PORT
- **5 FOAM** BALL (3)
- 6 DOGTROPHY STRAP
- **7** VERTICAL STAND *



^{*} Accessory optional

HOW TO CHARGE

- ▶ Plug the adapter into the charging port 4
- ▶ Plug the adapter into a wall plug
- While charging the ON/OFF LED ② will turn green and start blinking
- ► When fully charged: The ON/OFF LED 2 light is ON
- ► Full charge takes ± 4 hours, depending on which adapter is used
- The battery can last up to 5 days in STANDBY MODE (DOGTROPHY ON)

Note: Don't store the **DOGTROPHY** for a long time with an empty battery if you want to keep good performance of the **DOGTROPHY**. Charge the Dogtrophy at least once a month

HOW TO START

- ▶ Press the ON/OFF button 2 to start the **DOGTROPHY**
- ► The ON/OFF LED 2 will start blinking very quickly
- ▶ Press one stimulation button of the remote control until the ON/OFF LED 2 stop blinking quickly
- ► The ON/OFF LED 2 blink once every 5 seconds
- ▶ Press the stimulation button once more to start again the DOGTROPHY's mechanism
- ► This operation must be done each time the **DOGTROPHY** is started

6 **DOGTROPHY** BIG 2021 **▶** 7

ACCESSORIES (optional*)



*Not included

8

ATTENTION

- ▶ DO NOT USE OTHER BALLS THAN THE BRAND WE DELIVER
- ► DO NOT USE MORE THAN 3 BALLS BY ADDING ANOTHER TUBE ON TOP OF YOUR **DOGTROPHY**
- NEVER OPERATE MANUALLY THE PINS AT THE INSIDE
- NEVER TRY TO BLOCK OR HOLD THE PINS (MANUALLY) AT THE INSIDE OF THE TUBE
- **DOGTROPHY** IS NOT WATERPROOF
- ▶ DO NOT SUBMERGE UNDER WATER,
- ▶ PROTECT THE **DOGTROPHY** FROM RAIN
- DO NOT PUT ANY OIL OR OTHER LUBRICANT ON THE PINS INSIDE OF THE PLASTIC TUBE
- ► DO NOT USE **DOGTROPHY** UNDER OR ABOVE EXTREM T° (-20°C OR +40°C)

RECYCLING

Standards applicable to waste electrical and electronic devices state that they must be recycled.

If you are no longer using this material or if it cannot be repaired, do not throw it away in the usual household rubbish.

Return it to the vendor or contact Martin System® customer service for further information.



TECHNICAL SPECIFICATIONS

▶ DOGTROPHY

Dimensions (mm)	320 x 136 x 210
Weight (g)	1871,4
Power supply	5V – 2A
Range	200m
UHF frequency UHF power	869.5MHz
Antenna	External dipole antenna
Operating Temperature	-20° to 40°C
Waterproof	NO

10 **DOGTROPHY** BIG 2021 **▶** 11

WARRANTY

Martin System® quarantees its equipment against manufacturing defects for 2 years, covering parts and labor. This warranty covers all faults that occur under normal operating conditions. Faults arising from accidents and/or improper use are not covered. The warranty does not cover any of the following:

- Replacement of batteries.
- ▶ Replacement of the strap.
- ► Transport risks involved in returning the product to Martin System[®].
- ▶ Damage to the product as a result of negligence or an error on the part of the user.
- ▶ Damage to the product as a result of repairs made by nonauthorized persons.
- The liability for damage caused by the improper use of the product or a breakdown.

In the case of a defect, the device will, at the discretion of Martin System[®], be repaired or exchanged.

To benefit from this warranty, you must send within ten days the warranty certificate that accompanies the device. The warranty does not cover devices for which the warranty certificate has not been filled in and returned to Martin System®.



CONFORMITY

DECLARATION OF "CE" CONFORMITY

Declaration of Conformity (DoC) Directive R&TTE 1999/5/CE

MARTIN SYSTEM®

declares that the device **DOGTROPHY** complies with all the terms of the European Directive No 1999/5/CE of 07/04/99

And complies with the following standards: SAFETY (art 3.1.a): EN 60950 / EMC (art 3.1.b): EN 300.489-3 V1.4.1 SPECTRUM (art 3.2): EN 300.220-3 V1.1.1

Place and date of this document: Lantin, 15 October 2021

MARTIN SYSTEM®

Rue Joseph Martin, 35 - 4450 LANTIN - BELGIUM Signed by or for the manufacturer:

Name: Michael Bellon / Position: Director





Cutting-edge **technology** ▶ **Nature** in simple ways

Rue Joseph Martin, 35 - B-4450 Lantin - Belgium +32(0)4 263 96 05 - info@martinsystem.com www.martinsystem.com